

vsezip.ru

For internal use only! +7(812)987-08-81

Convection oven

MIWE econo

8.0604

Version: 0.2

No part of this documents must by reproduced or processed, copied, or distributed using electronic systems without the prior written consent of the publisher (MIWE Michael Wenz GmbH) in any form (print, foto copy, microfilm).

The same holds true for the simple forwarding of these instructions or the disclosure of the contents.

MIWE Michael Wenz GmbH
P.O.D. 20, D-97448 Arnstein, Germany
Phone +49-(0)9363-666
Fax +49-(0)9363-68 8422
e-mail originalteilede@miwe.de
www.miwe.com



Water installation

Position number	Short descr. of the item	Item No.	Page
1	Ventil.Magn.1- 1/8-S-230/50 AW	505210.00	6
2	Wasserzähler "Flowmeter FH20" 1/4"	507570.02	6
3	Steckverschraubung -L G1/4"- 8 MS	505207.60	6
4	Nippel-red. Ms 1/4x1/8	507518.07	6
5	Gerätesteckdose Wasserzähler	505212.08	6
6	Reduziernippel 3/8"i-1/8"aMS	507557.01	7
7	Winkelstück MS 3/8"a-3/8"a	507521.01	7
8	Reduziernippel kpl.	187611.00	7
9	Kunststoff-Sieb Typ "C"	505210.01	7

Steam

Position number	Short descr. of the item	Item No.	Page
10	Ventilator Axial DC 40x 40x20	506010.10	8
11	Schelle-Gewinde 25- 40	507436.00	8
12	Winkel*3092* RG 90° i/a 1"	508515.01	8
13	Motorkugelhahn 230V 90° (Stecker)	527567.10	8
14	Spritzrohr-Außenteil kpl.	081061.60	8
15	Ventil.Luft.Rücksch. H-QS-8	505200.32	8
16	Steckverbinder -Y 8- 8- 8 MS	505207.11	8
17	AVS-Steckverbinder-gerade-10-8	505207.12	9
18	PTFE-Rohr 8 x 6 Natur	505204.12	9
19	Schwadenabgang Anbauteil kpl.	080566.90	9
20	Dichtung Schwadenkanal	088512.00	9
21	Lüftermotor L9	504633.53	9
22	Graphit-Dichtring f. Gußkörper	088216.00	10
23	Heizregister 10,5 kW 230V (Stecker)	087711.50	10
24	Dichtung Spritzrohr	187906.00	10
25	Ventilatorrad	087374.00	10
26	Spritzrohr-Innenteil kpl. 8.0604	081061.70	10
27	Dichtung Welle URF-B17-108-HS	505508.03	10

Baking chamber

Position number	Short descr. of the item	Item No.	Page
28	Ansaugblech kpl.	081058.70	11
29	Auflageneinsatz 60x40 li kpl.	187342.85	11
30	Auflageneinsatz 60x40 re kpl.	187341.85	11
31	Fühler Temp. D=5mm PT1000 L180	504006.05	12
32	Türdichtung l=2820 AE 8.0604 geklebt	189016.03	12
33	EGO STB 3pol. 1890mm Kapillar 355°C-20K	504024.30	12

Baking chamber door

+7(812)987-08-81

Position number	Short descr. of the item	Item No.	Page
34	Glasscheibe 677x637x4	085364.70	13
35	Flachkopfschr. M 6x16 D921-A2	501360.03	13
36	Silikonlage D=20.0x8.0 gusto	507171.01	13
37	Dichtring D20xd6.5	505515.03	13
38	Griffgarnitur f. aeromat kpl.	087635.00	13
39	Kloben kurz rechts	506907.05	14
40	Kloben kurz links	506907.04	14
41	Innenscheibe kpl. TA re-li	085365.75	14
42	Silikonpuffer 9 x 6 x 15	507183.62	14
43	Halogenlampe G4 12V 20W	504588.13	15
44	Fassung-Halogen M3 G4/GZ4	504588.02	15
45	Silikonpuffer 13/7 x 7 H= 3	507183.60	15
46	Reed-Kontakt MK2/4-1A79-BV161	504127.04	15

Control system

Position number	Short descr. of the item	Item No.	Page
47	Bedienteil FP 12 S.u.anthrazit	504077.07A	16
48	BDS-Leistungsteil mit 32kByte FRAM	504078.90A	16
49	Fl.b.kabel 1500.St.a/r/i/g/t/t	504080.06	16
50	Steckbuchsenabdeckung RS 232	504068.00	16

Electrical installation

Position number	Short descr. of the item	Item No.	Page
51	Transformator Ringkern 230-150V UL 2.8A	505220.05	17
52	Ringtrafo 230/208V-11.5/20V UL	505235.08	17
53	Kondensator 25yF (Flachsteckan.)	505233.47	17
54	Sich. Autom. Moeller 1p D6 (PXL)	504346.62	17
55	Sich. Autom. Moeller 1p B16 (PXL)	504348.61	17
56	Printrelais-Sockel	504299.07	18
57	Printrelais 40.61.8.230 1W/16A	504296.00	18
58	Printrelais-Haltebügel 095.91	504300.02	18
59	Printrelais 44.52.9.012.0000	504298.01	18
60	RC-Modul 99.80.0 110-240VAC/DC	505255.03	19
61	Printrelais-Diode	504275.04	19
62	Endklammer TS35 249-117	504399.00	19
63	4-L.D-Klemme 2.5 grau 280-833	504396.01	19
64	4-L.D-Klemme 2.5 blau 280-834	504397.01	19
65	Endplatte 2.5 orange 280-315	504398.02	20
66	Kleinschutz LC1-K0610 P72	504202.07	20



Electrical installation


Position number	Short descr. of the item	Item No.	Page
67	Brückengleichrichter B80/70-25	505244.00	20
68	Kondensator 25yF (Flachsteckan.)	505233.47	20
69	Schütz 230V LC1-D32 -P7	504204.37	20
70	Kondensator liegend 4700 µF	505233.10	21
71	4-L.PE-Klemme 2.5 gr/ge280-837	504400.01	21
72	4-L.D-Klemme 2.5 blau 280-834	504397.01	21
73	4-L.D-Klemme 2.5 grau 280-833	504396.01	21
74	RC-Glied 250VAC 220nF 47R	504215.02	21
75	Lautsprecher (Aufbau)	505224.01	22
76	Ventilator Axial Std. W2S 130	506012.06	22
77	RC-Glied 110..240VAC 199-MSMA1	504215.01	22



Accessories

Position number	Short descr. of the item	Item No.	Page
78	Überspielkabel DS 3 pol 130cm	504073.29	23
79	Kantenschutz schwarz 1010-02	505511.01	23
80	Kaltgeräte-Einbausteckdose	504943.12	23
81	LOCTITE TYPE 243 50ml	507536.06	23
82	Dichtband Gewinde DVGW 0.1mm	507516.02	23
83	Dichtungskartusche DOW CORNING	507353.05	23
84	Schlauch-Dampf (3/4") 19x6.5	507431.00	23














28


+7(812)987-08-81



29



30






31



32



33







39




Block short right



40



Block short left



41



42



vsezip.ru

+7(812)987-08-81



43



44








45



46









vsezip.ru



+7(812)987-08-81



56



57




58




59





60



61



62



63




64






65



66



67



68



69





vsezip.ru

+7(812)987-08-81



vsezip.ru

+7(812)987-08-81



78



79



80



81



82



83



84

